

Protect your Rotating equipment



LabTecta GOULDS PUMPS


Advanced Non-contacting
Bearing Protection



GOULDS 3196	DIMENSIONS	BEARING LOCATION	LABTECTA PRODUCT CODE	REPAIR KIT #
ST, STX	0.875 X 1.250	MOTOR SIDE	LA07PP001GO00021M	LA07GO00021M-RK
	1.375 X 2.835	PUMP SIDE	LA11PP001GO00021P	LA11GO00021P-RK
MT, MTX	1.125 X 2.000	MOTOR SIDE	L1I09-PP-001-I16-	L1I09-RK4
	1.750 X 2.875	PUMP SIDE	L1I14-PP-001-I23-	L1I14-RK4
LT, LTX	1.875 X 2.750	MOTOR SIDE	L1I15-PP-001-I22-	L1I15-RK4
	2.125 X 2.875	PUMP SIDE	L1I17-PP-001-I23-	L1I17-RK4
XLT, XLTX	2.375 X 3.250	MOTOR SIDE	L1I19-PP-001-I26-	L1I19-RK4
	2.500 X 3.250	PUMP SIDE	L1I20-PP-001-I26-	L1I20-RK4

GOULDS 3175	DIMENSIONS	BEARING LOCATION	LABTECTA PRODUCT CODE	REPAIR KIT #
S	2.375 X 3.250	MOTOR SIDE	L1I19-PP-001-I26-	L1I19-RK4
	2.500 X 3.250	PUMP SIDE	L1I20-PP-001-I26-	L1I20-RK4
M	3.125 X 4.125	MOTOR SIDE	L1I25-PP-001-I33-	L1I25-RK4
	3.312 X 4.125	PUMP SIDE	L1I271PP-001-I33-	L1I271-RK4
L	4.125 X 5.250	MOTOR SIDE	L1I33-PP-001-I42-	L1I33-RK4
	4.312 X 5.500	PUMP SIDE	L1I351PP-001-I44-	L1I351-RK4
XL	4.312 X 5.500	MOTOR SIDE	L1I351PP-001-I44-	L1I351-RK4
	5.000 X 6.250	PUMP SIDE	L1I40-PP-001-I50-	L1I40-RK4

GOULDS 3180	DIMENSIONS	BEARING LOCATION	LABTECTA PRODUCT CODE	REPAIR KIT #
S	48mm x 70mm	MOTOR SIDE	L1M048PP-001-M070	L1M048-RK4
	55mm x 80mm	PUMP SIDE	L1M055PP-001-M080	L1M055-RK4
M	48mm x 70mm	MOTOR SIDE	L1M048PP-001-M070	L1M048-RK4
	60mm x 85mm	PUMP SIDE	L1M060PP-001-M085	L1M060-RK4
L	70mm x 95mm	MOTOR SIDE	L1M070PP-001-M095	L1M070-RK4
	70mm x 95mm	PUMP SIDE	L1M070PP-001-M095	L1M070-RK4
XL	85mm x 110mm	MOTOR SIDE	L1M085PP-001-M110	L1M085-RK4
	85mm x 110mm	PUMP SIDE	L1M085PP-001-M110	L1M085-RK4




*For "I" series Pumps replace the "PP" with "SP"
Example: L1I14-SP-001-123-




Additional sizes and Styles available



Pillow Blocks



Top Entry



Air Purge



Stainless Steel



Split



Electric Motors



Cooling Towers



Gear Boxes



Paper Machine Rolls



Hydropulpers

Paper Mills

Coal conveying

Rock Quarries

Mining

Refineries

Contact the LabTecta Distributor in your area or contact us direct at:
Telephone 865-531-0192 Fax 865 675-2437 or LabTectaUSA@AESSEAL.com



Distributed by:
Engineered Sealing Solutions
PO Box 3005
Sulphur, Louisiana 70664
Ph: (337) 882-9943 Fax: (337) 882-9945
Email: sales@ess4solutions.com
Website: www.ess4solutions.com
L-US-LABTECTA-G POSTER-2